

NOTES:

1. SUBSTRATE:
SCHOTT NG9

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





2. FINE GRIND SURFACE

3. COATING SPECIFICATION:
S1 & S2:NONE

4. OPTICAL DENSITY: 2.0


5. TRANSMISSION (%): 1.0

6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2	 THIRD ANGLE PROJECTION		TITLE	SCHOTT NG9, 2.0 OD, 25mm DIA., ABSORPTIVE ND FILTER	
SHAPE	PLANO	PLANO			TITLE		
SURFACE QUALITY	80-50	80-50			TITLE		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	16667	SHEET 1 OF 1