

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**





NOTES:

- 1. SUBSTRATE: BOROFLOAT33
- 2. COATING

DURABILITY:
PHYSICAL: MIL-C-48497A, SECTION 3.4.1
ENVIRONMENTAL: MIL-STD-810F, SECTION 507.4

PERFORMANCE SPECIFICATIONS @ 0° AOI
T(AVG): ≥85% from 500 - 900nm
T(AVG): ≤1% from 1025 - 1250nm
CUT-OFF WAVELENGTH: T(ABS) = 50% @ 950nm ± 19nm

- 3. ROHS COMPLIANT



SHORTPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø11.25	Ø11.25
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EO® **Edmund Optics**®



ALL DIMS IN mm

TITLE

FILTER OD2 SHORTPASS 950nm 12.5mm

DWG NO

15255

SHEET
1 OF 1