





FOCAL LENGTH (EFL): $10 \pm 0,1$
 BACK FOCAL LENGTH (BFL): $8,1$

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R 5,17 CX Øe 6,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ -		GLASS N-BK7 517/642 Nd: 1,517 Vd: 64,17	R ∞ PL Øe 6,3 (λ) - 3/ 3 (0,5) λ=632,8 nm 4/ 5,8' 5/ 40 - 20 6/ -	
PROTECTIVE CHAMFERS AS NEEDED ROHS: COMPLIANT SCALE: NONE λ = 587,6nm SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110		FIRST ANGLE PROJECTION  ALL DIMS IN: mm	 Edmund Optics® TITLE 7mm Dia x 10mm FL, Uncoated, Plano-Convex Lens DWG NO 28947 SHEET SIZE A4 SHEET 1 OF 1	