





f' : $7 \pm 0,07$

BACK FOCAL LENGTH (BFL): 5,5



LEFT SURFACE			MATERIAL	RIGHT SURFACE					
R 5,5 CX Øe 6,3 λ AR Rave(400nm - 700nm, 0°) < 1,75% 3/ 3 (0,5) λ=632,8 nm 4/ 3,82' 5/ 40 - 20 6/ - P			GLASS N-SF11 785/258 Nd: 1,785 Vd: 25,68	R ∞ PL Øe 6,3 λ AR Rave(400nm - 700nm, 0°) < 1,75% 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 6/ - P					
PROTECTIVE CHAMFERS AS NEEDED <table><tr><td>ROHS: COMPLIANT</td><td>SCALE: NONE</td><td>λ = 587,6nm</td></tr></table> SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING INDICATIONS IN ACCORDANCE WITH ISO 10110			ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm	FIRST ANGLE PROJECTION ⊕	EO ® Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm							
			TITLE	7mm Dia x 7mm FL, MgF2 Coated, Plano-Convex Lens					
			ALL DIMS IN: mm	DWG NO	71293	SHEET SIZE A4			
					SHEET 1 OF 1				