



- NOTES:
- 1. SUBSTRATE MATERIAL: N-BK7
 - 2. ROHS COMPLIANT
 - 3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: NONE
 - S2: Ravg >89% @ 250 - 450nm
 - Ravg >85% @ 250 - 700nm

4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | S1 | S2 |
|---------------------|---------------------|---------------------|
| SHAPE | PLANO | PLANO |
| ANGEL TOL. (arcmin) | ±2 | ±2 |
| SURFACE QUALITY | 40-20 | 40-20 |
| SURFACE FLATNESS | λ/4 | λ/4 |
| BEVEL | PROTECTED AS NEEDED | PROTECTED AS NEEDED |

| | | | |
|------------------------|--|----------------|--|
| THIRD ANGLE PROJECTION | | Edmund Optics® | |
| ALL DIMS IN mm | | TITLE | 25mm, UV Enhanced Aluminum, N-BK7 90° Specialty Mirror |
| DWG NO | | 25-711 | SHEET 26 OF 31 |